

# Sack Master


## Large Range of High Quality Sack Samplers

The Sack Master has been specially designed to take samples through the side of a sack. A range of sample collection methods are available.

Type: Single point

Material: 316 stainless steel

- Operation:
1. Insert the sampler through the side of the sack.
  2. Angle sampler downwards to allow the product to flow into the sample collecting container
  3. Seal the hole using an Ultra Adhesive Label



End Fittings:

### (A) Plain

- Sample collecting bag is held over end of sampler
- Plain end
- Electropolished



### (B) End Cap

- Cap screws on to end of Sack Sampler
- Easily removed for cleaning
- Sample is retained in Sack Sampler
- Electropolished



### (C) Bottle Adapter

- Adapter screws on to end of Sack Sampler
- Sample is collected in either a 250ml or 500ml bottle
- After sampling unscrew bottle and screw on the plastic bottle cap
- Electropolished



| Part No.                                                             | Sampler Description                                          | Sampler End Fitting |
|----------------------------------------------------------------------|--------------------------------------------------------------|---------------------|
| 1320A-01                                                             | Sack Master P                                                | Plain               |
| 1320B-01                                                             | Sack Master EC                                               | End Cap             |
| 1320C-01                                                             | Sack Master BA                                               | Bottle Adapter*     |
| * Sampler supplied with one 250ml Sample Bottle (Part No. 8165A-250) |                                                              |                     |
| <b>Accessories</b>                                                   |                                                              |                     |
| 8165A-250                                                            | Sampling Bottle - 250ml - HDPE - for use with bottle adapter |                     |
| 8165A-500                                                            | Sampling Bottle - 500ml - HDPE - for use with bottle adapter |                     |
| 8001A-500                                                            | Cleaning Brush - 500mm length                                |                     |
| Storage Cases                                                        | Please download brochure for further information             |                     |