## **COFFEE** LABORATORY

## **Programmable Digital Refractometer**

## SP 3000

## Create your own custom scales

This programmable refractometer comes preloaded with the commonly used Brix (0 ~ 95%) and nD (refractive index) scales. In addition, you may create your own custom scales. An unlimited number of scales can be stored in the software's database. Transfer these from your computer to the three numbered display positions on the Programmable Refractometer using the built-in RS232 computer interface. Scales can be loaded and unloaded from your database to your refractometer at any time. Test results can be saved to your computer, graphed and analyzed. Reads samples as small as 0.4ml with full scale accuracy of 0.2% using CCD scanner (linear scanned array imaging) technology. Measurement results, unit of measure, and sample temperature are all displayed on the large LCD, and visual alarms are indicated by a red LED. The programmable refractometer's sophisticated microprocessor provides automatic calibration, automatic temperature compensation, and automatic shutoff (after 3 minutes). A sturdy water resistant case protects the electronics from wet environments and makes for easy clean ups. Features one button calibration to distilled water and indicates when the battery should be replaced (5000 readings). Scratch resistant sapphire crystal lens. Comes ready to use with a 9V battery, distilled water, transfer pipette, cable, AC adaptor, software, instructions and a protective case.

dim: 7" × 4" × 2½" (180 × 100 × 65 mm). Weight: 18 oz (500 g).

No.	Description	Each	Unit of Measure	Range	Res.	Accuracy
655 SP3000	Programmable Refractometer	\$1090.00	Temperature °C	0 ~ 40°	0.1	1°
000 SF3000		<i></i>	Temperature °F	32 ~ 104°	0.1	2°
			Brix	0~95%	0.1%	±0.2%
			Refractive Index + up to 3 custom scales	1.3330 ~ 1.5318	0.0001	±0.001



	R SCIENTIFIC Refractomete	ar Software			_i0
ie ge ,316	etting Eurotion Help		2		
22		0 3			
	Value:		Tempi		
	1.3330 nD		80.		
	Scale Name	nD	Zero Statu:	Zero Point Normal	9
	Temperature Compensation	Enabled	High Linit Alam Value:	Disabled	Ø
	Neassement Time: 6/2	/2007/ 09:38:40	Low Linit Alam Value:	Disabled	ø
MS OPE	IN 🕘 CONS opened success	έ,êγi		9600 8-N-2	

